


PORTRAIT







— STANDARD OPTIONS:

Standard sizes					
No.	Part No.				
1	Mir0785- Acc.00				
2	Mir0738- Acc.00				
3	Mir0739- Acc.00				
4	Mir0749- Acc.00				
5	Mir0741- Acc.00				

	Α				
	H x <u>W</u>				
_	mm	inch			
	52 x <u>100</u>	2 x <u>3.93</u>			
	76 x <u>150</u>	3 x <u>5.90</u>			
	127 x <u>200</u>	5 x <u>7.87</u>			
	152 x <u>217</u>	6 x <u>8.54</u>			
	152 x <u>221</u>	6 x <u>8.70</u>			

		\mathbb{A}
Нх	: <u>W</u>	
า	inch	
<u>100</u>	2 x <u>3.93</u>	102
<u>150</u>	3 x <u>5.90</u>	152
<u> 200</u>	5 x <u>7.87</u>	203
<u> 217</u>	6 x <u>8.54</u>	217
221	6 x 8 70	221

	, a .				
	H x <u>W</u>				
	mm	inch			
	102 x <u>100</u>	4 x <u>3.93</u>			
	152 x <u>150</u>	6 x <u>5.90</u>			
	203 x <u>200</u>	8 x <u>7.87</u>			
	217 x <u>217</u>	8.54 x <u>8.54</u>			
	221 x <u>221</u>	8.70 x <u>8.70</u>			

,	/YY A				
	H x <u>W</u>				
	mm	inch			
	152 x <u>100</u>	6 x <u>3.93</u>			
	203 x <u>150</u>	8x <u>5.90</u>			
	254 x <u>200</u>	10 x <u>7.87</u>			
	297 x <u>217</u>	11.6 x <u>8.54</u>			
	280 x <u>221</u>	11 x <u>8.70</u>			
		mm 152 x 100 203 x 150 254 x 200 297 x 217			

1. Select the size of the sign from **Extrusion Standard sizes** table.

- 2. Select an accent from the Accent Bar Sizes table.
- 3. Matche the accent size to the sign size. The sizes are underlined in both tables
- 4. Select the Accent location on the sign frame parallel to the location of the end caps.

Accent Bar Sizes

		Accer	nt -H 1	Extrusion <u>W</u> 100 _{mm} /3.9"	Extrusion <u>W</u> <u>150mm/5.9"</u>	Extrusion <u>W</u> 200 _{mm} / <u>7.87</u> "	Extrusion <u>W</u> <u>217_{mm}/3.9"</u>	Extrusion <u>W</u> <u>221_{mm}/<u>8.7</u>"</u>
No.	Accent	mm	inch	<u>W1 120mm/4.72"</u>	<u>W1 180</u> mm/7.08"	<u>W1 252mm/9.92</u> "	<u>W1</u> 272 _{mm} /10.7"	<u>W1 272mm/10.7</u> "
1	Acc.01	6	0.24	•	•			
2	Acc.02	10	0.39		•	•	-	•
3	Acc.03	13	0.59			•	•	•
4	Acc.04	20	0.79		•	•		•
5	Acc.05	40	1.57		•	•		
6	Acc.06	25	1		•	•		•
7	Acc.07	25	1					

Jupiter / Orion Accentia family Desktop



EXTRUSION finish/color options: are made from high quality aluminum 6063 with an anodized or oven cured coating

1. Clear anodized aluminum

а

INSERT OPTIONS:

- 1. Graphic sign fronts: engraved, laminated, silk screened, Imprinted with braille or photo metal finished
- 2. Applied vinyl on aluminum insert
- 3. 1. .040 aluminum backed photopolymer w/ raised symbols/copy and ADA compliant braille. Tip symbols/copy to contrast background. braille to remain background color
- 4. Acrylic cover w/ paper insert5. Digital printing onto anodized aluminum by Primodize ® or direct on clear cover

END CAPS finish/color options:

- 1. Clear anodized aluminum
- 2. Can be painted or powder coated
- 3. Gray or black ABS plastic

C1

Base finish/color options:

1. Mirtec clear anodized aluminum

ACCENT BAR (available page no.*) finish/color options:

- 1. Standard Mirtec anodized colors
- 2. Can be painted or powder coated

