
PORTRAIT



Standart sizes				
No.	Part No.			
_1	Mir2037- Acc.00			
2	Mir2038- Acc.00			
3	Mir2039- Acc.00			
4	Mir2040- Acc.00			

	A			
	H x <u>W</u>			
	mm	inch		
.00	40 x <u>62</u>	1.57 x <u>2.44</u>		
.00	76 x <u>102</u>	3 x <u>4.01</u>		
.00	102 x <u>152</u>	4.01 x <u>6</u>		
.00	152 x <u>222</u>	6 x <u>8.74</u>		

AA						
	Нх	H x <u>W</u>				
1	mm	inch				
2.44	62 x <u>62</u>	2.44 x <u>2.44</u>				
l.01	102 x <u>102</u>	4.01 x <u>4.01</u>				
x <u>6</u>	152 x <u>152</u>	6 x <u>6</u>				
<u>3.74</u>	222 x <u>222</u>	8.74 x <u>8.74</u>				

/111							
	H x <u>W</u>						
	mm	inch					
	102 x <u>62</u>	4.01 x <u>2.44</u>					
	152 x <u>102</u>	5.98x <u>4.01</u>					
	203 x <u>152</u>	8 x <u>5.98</u>					
	280 x <u>222</u>	11 x <u>8.74</u>					

 $\Delta\Delta\Delta$

1.Select the size of the sign from **Extrusion Standard sizes** table.

- 2. Select an accent from the Accent Bar Sizes table.
- 3. Matche the accent size to the sign size. The sizes are underlined in both tables
- 4. Select the Accent location on the sign frame parallel to the location of the end caps.

Accent Bar Sizes

/ 1000	Accent bai Sizes							
			Accen	t -H 1	Extrusion <u>W</u> <u>102 mm/<u>4</u>"</u>	Extrusion <u>W</u> <u>152_{mm}/<u>6</u>"</u>	Extrusion <u>W</u> 222 _{mm} / <u>8.74</u> "	Extrusion W 304 _{mm} /11.9"
No.	Accent		mm	inch	<u>W1 110mm/4.33</u> "	<u>W1 161</u> mm/6.3"	<u>W1</u> 231 _{mm} /9.1"	<u>W1</u> <u>315</u> mm/ <u>12.4</u> "
1	Acc.01		6	0.24	•			
2	Acc.02		10	0.39	•	•	•	
3	Acc.03		13	0.59				
4	Acc.04		20	0.79	•			
5	Acc.05		40	1.57				•
6	Acc.06		25	1	•	•		
7	Acc.07		25	1				

Venus Accentia Sign Family Desktop

NOTES:

а

EXTRUSION finish/color options: are made from high quality aluminum 6063 with an anodized or oven cured coating

1. Clear anodized aluminum



INSERT OPTIONS:

- 1. Graphic sign fronts: engraved, laminated, silk screened, Imprinted with braille or photo metal finished
- 2. Applied vinyl on aluminum insert
- 3. 1. .040 aluminum backed photopolymer w/ raised symbols/copy and ADA compliant braille. Tip symbols/copy to contrast background. braille to remain background color
- 4. Acrylic cover w/ paper insert
- 5. Digital printing onto anodized aluminum by Primodize ® or direct



END CAPS finish/color options:

- 1. Clear anodized aluminum
- 2. Can be painted or powder coated
- 3. Gray or black ABS plastic



Base finish/color options:

1. Mirtec clear anodized aluminum



ACCENT BAR (available page no.*) finish/color options:

- 1. Standard Mirtec anodized colors
- 2. Can be painted or powder coated



